

Indicating insert MFL-230AC

Part number: 10005

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Product weight	14 g
Electrical connection	Form B As per industrial standard (11 mm)
Nominal operating voltage AC	230 V
Mains frequency	50 Hz ... 60 Hz
Permissible voltage fluctuations	-20 % / +15 %
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-20 °C ... 60 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA6-reinforced