

End stop limit switch SDK-4-PK-3

Part number: 10033

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Valve function	3/2, closed, monostable
Actuation type	Mechanical
Normal nominal flow rate (normalized to DIN 1343)	16 l/min
Pneumatic working port	PK-3
Operating pressure	0 bar ... 8 bar
Structural design	Ball seat
Reset method	Mechanical spring
Nominal width	0.6 mm
Exhaust air function	With flow control option
Sealing principle	Soft
Type of control	Direct
Flow direction	Non-reversible
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 80 °C
Ambient temperature	-10 °C ... 80 °C
Actuating force	17 N
Type of mounting	With through-hole
Pneumatic connection 1	PK-3
Pneumatic connection 2	PK-3
Pneumatic connection 3	Not ducted