

# Pressure gauge OH-8-BL

Part number: 10090

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Symbol                                   | 00991500   |
| Operating pressure                       | -0.1 MPa ... 0.8 MPa   |
| Operating pressure                       | -1 bar ... 8 bar   |
| Operating pressure                       | -14.5 psi ... 116 psi  |
| Explosion prevention and protection      | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -10 °C ... 60 °C   |
| Pneumatic connection                     | Barbed fitting PK-3  |
| Note on materials                        | RoHS-compliant   |