


# Pressure gauge OH-8-GE

Part number: 10091

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Symbol	00991500
Operating pressure	-0.1 MPa ... 0.8 MPa
Operating pressure	-1 bar ... 8 bar
Operating pressure	-14.5 psi ... 116 psi
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Pneumatic connection	Barbed fitting PK-3
Note on materials	RoHS-compliant