


Suction cup insert OASI-40

Part number: 1048881

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Operating pressure	0 bar ... 0.95 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-:]
LABS (PWIS) conformity	VDMA24364-A1-L
For use in the food industry	See supplementary material information
Ambient temperature	5 °C ... 50 °C
Product weight	2.9 g
Type of mounting	Insertable
Note on materials	RoHS compliant
Suction-cup insert material	Protective grounding
Ejector pulse suitability	≤5 bar
Mounting position	Inner thinning