

Rod clevis SGA-M16X1,5

Part number: 10768

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	M16x1.5
Radial deviation +/-	5 mm
Angle compensator +/-	120 deg
Mounting position	Any
Threaded connection	External thread M16x1.5
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	4 kN
Product weight	512 g
Note on materials	RoHS compliant
Bolt material	Steel, galvanized
Material of rod eye	Steel Galvanized
Fuse material	Spring steel, galvanized