



# Front panel valve SV-5-M5-B

Part number: 11914

FESTO



 General operating condition

## Data sheet

Feature	Value
Valve function	5/2-way, monostable
Actuation type	Manual
Normal nominal flow rate (normalized to DIN 1343)	95 l/min
Operating pressure	0 MPa ... 0.8 MPa
Operating pressure	0 bar ... 8 bar
Structural design	Poppet valve with spring return
Reset method	Mechanical spring
Nominal width	2.3 mm
Sealing principle	Soft
Mounting position	Any
Type of control	directly
Symbol	00991339
Lap	Positive overlap
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Actuating force	17 N
Product weight	53 g
Type of mounting	With through-hole
Pneumatic connection 1	M5
Seals material	NBR
Housing material	Polymer Brass