

# Barbed bulkhead connector SCN-PK-3

Part number: 11972

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	1.9 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Pneumatic connection 1	for pneumatic tubing outside diameter 4 mm
Note on materials	RoHS compliant
Housing material	Aluminum
Nut material	Steel, galvanized