

# Pneumatic muffler AMTE-M-LH-G14

Part number: 1205861

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

| Feature                                  | Value  |
|--|--|
| Mounting position                        | Any  |
| Pack size                                | 20   |
| Symbol                                   | 00991473   |
| Operating pressure                       | 0 MPa ... 1 MPa  |
| Operating pressure                       | 0 bar ... 10 bar   |
| Flow rate with respect to atmosphere     | 3140 l/min   |
| Explosion prevention and protection      | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Information on operating and pilot media | Operation with oil lubrication possible                            |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Noise level                              | 83 dB(A)   |
| Ambient temperature                      | -40 °C ... 80 °C   |
| Product weight                           | 13 g   |
| Pneumatic connection                     | G1/4   |
| Cushioning insert material               | Bronze   |
| Material of screwed plug                 | Brass  |
| Note on materials                        | RoHS-compliant   |