

# Pneumatic muffler AMTE-M-LH-N38

Part number: 1206991

FESTO



[PDF](#) [General operating condition](#)

## Data sheet

| Feature                                  | Value   |
|--|---|
| Mounting position                        | Any   |
| Pack size                                | 10  |
| Symbol                                   | 00991473                                      |
| Operating pressure                       | 0 MPa ... 1 MPa                               |
| Operating pressure                       | 0 bar ... 10 bar                              |
| Flow rate with respect to atmosphere     | 5365 l/min                                    |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Lubricated operation possible                 |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress                      |
| LABS (PWIS) conformity                   | VDMA24364-B2-L                                |
| Noise level                              | 83 dB(A)                                      |
| Ambient temperature                      | -40 °C ... 80 °C                              |
| Product weight                           | 29 g  |
| Pneumatic connection                     | 3/8 NPT                                       |
| Cushioning insert material               | Bronze  |
| Material of screwed plug                 | Brass   |
| Note on materials                        | RoHS compliant                                |