

# Parallel kit EAMM-U-60-D32-55A-91-S1

Part number: 1210450

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	60
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP65
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	26.7 kgmm <sup>2</sup>
No-load driving torque	0.07 Nm
Transferable torque	3 Nm
Product weight	1100 g
Interface code, actuator	D32B
Interface code, motor in	55A
Note on materials	RoHS compliant