

Plastic tubing PU-13-SW

Part number: 12133

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	17.6 mm
Bending radius relevant for flow rate	83 mm
Inside diameter	13 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-35 °C ... 60 °C
Product weight by length	0.133 kg/m
Pneumatic connection	For barbed fitting, inside diameter 13 mm, with union nut
Color	Black
Shore hardness	A 86 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)