


Parallel kit EAMM-U-110-S62-100A-207

Part number: 1217381

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Size	110
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	799 kgmm ²
No-load driving torque	0.3 Nm
Transferable torque	25 Nm
Product weight	6900 g
Interface code, actuator	S62
Interface code, motor in	100A
Note on materials	RoHS-compliant