

# Coupling EAMC-30-35-8-11

Part number: 123042

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Diameter of holder 1	8 mm
Diameter of holder 2	11 mm
Size	30
Nominal length	35 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	6.1 kgmm <sup>2</sup>
Transferable torque	8.2 Nm
Product weight	45 g
Note on materials	RoHS compliant