

# Solenoid coil MSN1G-24DC-OD

Part number: 123060

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Min. pick-up time	10 ms
Duty cycle	100%
Coil characteristics	24 V DC: 2.5 W
Permissible voltage fluctuations	-15 % / +10 %
Certification	c UL us - Recognized (OL)
LABS (PWIS) conformity	VDMA24364-C1-L
Temperature of medium	-10 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-10 °C ... 50 °C
Product weight	80 g
Electrical connection	3-pin Form A as per DIN EN 175301-803
Type of mounting	Clamped With retaining clamp With accessories
Housing material	PA
Material of pin contacts	Steel
Material of winding	Copper