

Push-in Y-connector CRQSY-10

Part number: 130659

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 5.6 mm |
| Tubing insertion depth | 25.5 mm |
| Mounting position | Any |
| Design | Y-shape |
| Pack size | 1 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi |
| Temperature-dependent operating pressure | -0.095 MPa ... 1 MPa |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar |
| Temperature-dependent operating pressure | -13.775 psi ... 145 psi |
| Information on operating pressure | Water: max. 0.6 MPa at max. 50 °C |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -15 °C ... 120 °C |
| Product weight | 52 g |
| No. of outlets | 2 |
| No. of supply lines | 1 |
| Usable connector cables | PFAN |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 10 mm |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 10 mm |
| Releasing ring color | Silver |
| Note on materials | RoHS-compliant |
| Housing material | High-alloy stainless steel |
| Releasing ring material | High-alloy stainless steel |
| Material of tubing seal | FPM |
| Material of tube retaining claw | High-alloy stainless steel |
| Thrust ring material | High-alloy stainless steel |