

Plastic tubing PUN-CM-10-SW

Part number: 130817

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	60 mm
Inside diameter	7 mm
Min. bending radius	30 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa ... 1 MPa
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-13.775 psi ... 145 psi
Surface resistance	0.01 MOhm ... 10 MOhm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C ... 60 °C
Product weight by length	0.05158 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Black
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)