


Flow control/muffler VFFK-C-K-R14-P

Part number: 133143

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Valve function | Sound pressure flow control function |
| Selection of additional function | with muffler |
| Pneumatic connection 1 | R1/4 |
| Adjusting element | Knurled screw |
| Type of mounting | Screw-in |
| Standard flow rate 6->0 bar | 0 l/min ... 420 l/min |
| Operating pressure | 0 bar ... 10 bar |
| Ambient temperature | 0 °C ... 60 °C |
| Type of seal on screwed plug | Coating |
| Mounting position | Any |
| Symbol | 00991451 |
| Operating pressure for entire temperature range | 0 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Temperature of medium | 0 °C ... 60 °C |
| Product weight | 25 g |
| Cushioning insert material | PE |
| Material of screwed plug | Brass, nickel-plated |
| Note on materials | RoHS-compliant |
| Material of adjusting screw | Brass, nickel-plated |