

# Clamping sleeve EAMH-50-8-C13.6-P

Part number: 1354094

FESTO



 [General operating condition](#)

## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 50                     |
| Mounting position      | Any                    |
| Max. rotational speed  | 6000 rpm               |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C ... 60 °C       |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -10 °C ... 60 °C       |
| Mass moment of inertia | 0.35 kgmm <sup>2</sup> |
| Product weight         | 16 g                   |
| Note on materials      | RoHS-compliant         |