

Clamping sleeve EAMH-60-9-C18.1-P

Part number: 1354098

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	60
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	1.5 kgmm ²
Product weight	39 g
Note on materials	RoHS-compliant