

Rod clevis CRSG-M20X1,5

Part number: 13572

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	M20x1.5
Mounting position	Any
Based on norm	ISO 8140
Threaded connection	Internal thread M20x1.5
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Ambient temperature	-40 °C ... 150 °C
Max. load capacity	9 kN
Product weight	757.8 g
Rod clevis material	High-alloy steel
Note on materials	RoHS compliant
Bolt material	High-alloy steel
Nut material	High-alloy steel
Fuse material	High-alloy steel