


Vacuum suction cup VASB-125-3/8-PUR-B

Part number: 1396067

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Suction cup height compensation | 25 mm |
| Nominal width | 7 mm |
| Suction cup diameter | 125 mm |
| Suction cup volume | 307 cm ³ |
| Effective suction cup diameter | 101.8 mm |
| Connection position | Top |
| Mounting position | Any |
| Symbol | 00991485 |
| Suction cup shape | Round bellows, 1.5 convolutions |
| Operating pressure | -0.095 MPa ... 0 MPa |
| Operating pressure | -0.95 bar ... 0 bar |
| Operating pressure | -13.775 psi ... 0 psi |
| Nominal operating pressure | -0.07 MPa |
| Nominal operating pressure | -0.7 bar |
| Nominal operating pressure | -10.15 psi |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | -20 °C ... 60 °C |
| Holding force at nominal operating pressure | 570 N |
| Product weight | 294 g |
| Type of mounting | Via vacuum connection |
| Vacuum connection | G3/8 |
| Color | Blue |
| Shore hardness | 60 +/- 5 |
| Material of screwed plug | Die-cast zinc |
| Note on materials | RoHS-compliant |
| Suction cup material | PUR |