

Vacuum suction cup VAS-8-M5-PUR-B

Part number: 1396086

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Suction cup height compensation	0.9 mm
Nominal width	2 mm
Suction cup diameter	8 mm
Suction cup volume	0.095 cm ³
Effective suction cup diameter	7.1 mm
Connection position	up
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, flat
Operating pressure	-0.095 MPa ... 0 MPa
Operating pressure	-0.95 bar ... 0 bar
Operating pressure	-13.775 psi ... 0 psi
Nominal operating pressure	-0.07 MPa
Nominal operating pressure	-0.7 bar
Nominal operating pressure	-10.15 psi
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-20 °C ... 60 °C
Holding force at nominal operating pressure	2.8 N
Product weight	4 g
Type of mounting	Via vacuum connection
Vacuum connection	M5
Color	Blue
Shore hardness	60 +/-5
Material of screwed plug	Brass
Note on materials	RoHS compliant
Suction cup material	PUR