

Manifold sub-base NAV-1/2-NPT-3C

Part number: 13999

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width	190 mm
Operating pressure	16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Sub-base mounting type	With through-hole
Pilot air port 12	NPT1/8-27
Pilot air port 14	NPT1/8-27
Pneumatic connection 2	NPT1/2-14
Pneumatic connection 4	NPT1/2-14