

Rotary actuator DRRD-20-180-FH-Y9A

Part number: 1427379

FESTO



 General operating condition

Data sheet

Feature	Value
Size	20
Cushioning angle	72 deg
Setting range of swivel angle for each end position	+10 /-190 deg
Swivel angle	180 deg
Cushioning	Internal hydraulic cushioning normal
Mounting position	Any
Structural design	Gear rack/pinion
Position sensing	For proximity sensor
Symbol	00991265
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-10 °C ... 60 °C
Theoretical torque at 6 bar	2.41 Nm
Permissible mass moment of inertia	0.125 kgm ²
Product weight	883 g
Type of mounting	With through-hole With internal thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Drive shaft material	Tempered steel
Cover material	Wrought aluminum alloy Anodized
Seals material	NBR TPE-U(PU)
Housing material	Smooth anodized