


Axial kit EAMM-A-M48-60H

Part number: 1456614

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal length	26 mm
Mounting position	Any
Max. rotational speed	6000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	39 kgmm ²
Transferable torque	21 Nm
Product weight	320 g
Interface code, actuator	M48
Interface code, motor in	60H
Note on materials	RoHS-compliant