


Intermediate position module DADM-EP-G6-10

Part number: 1492072

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	10
Mounting position	Any
Structural design	Positively driven motion sequence
Position sensing	Via proximity switch
Symbol	00991270
Operating pressure	3 bar ... 6 bar
Max. impact velocity	0.8 m/s
Maximum pivot time	150 ms
Repetition accuracy	±0.02 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Max. stop force	500 N
Product weight	154 g
Type of mounting	Via through-hole and centering sleeve
Pneumatic connection	M3
Note on materials	RoHS compliant
Seals material	PU
Housing material	Wrought aluminum alloy
Lever material	high-alloy stainless steel