

Programming cable NEBC-U1G4-K-1.8-N-U2G4

Part number: 1501332

FESTO



 General operating condition

Data sheet

Feature	Value
Cable designation	Without label holder
Mounting position	Any
Electrical connection 1	Straight plug, USB 2.0 type A, 4-pin
Electrical connection 1, function	Field device side
Electrical connection 1, design	Square
Electrical connection 1, connection type	Plug
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connection technology	USB 2.0 type B
Electrical connection 1, number of pins/wires	4
Electrical connection 1, occupied pins/wires	4
Electrical connection for input 1, connection pattern	00995727
Electrical connection 2	Straight plug, USB 2.0 type B, 4-pin
Electrical connection 2, function	Control side
Electrical connection 2, design	Square
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connection technology	USB 2.0, type A
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	4
Electrical connection 2, connection pattern	00995726
Cable length	1.8 m
Cable characteristic	Standard
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 Zone III
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	0 - No corrosion stress