

One-way flow control valve GRLA-3/8-NPT-B

Part number: 151555

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | Exhaust air flow control non-return function |
| Pneumatic connection 1 | 3/8 NPT |
| Pneumatic connection 2 | 3/8 NPT |
| Adjusting element | Slotted screw |
| Type of mounting | Screw-in |
| Ambient temperature | -10 °C ... 60 °C |
| Symbol | 00991452 |
| Operating pressure for entire temperature range | 0.3 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 4 according to ISO 14644-1 |
| Temperature of medium | -10 °C ... 60 °C |
| Note on materials | RoHS-compliant |
| Seals material | NBR |
| Hollow bolt material | Wrought aluminum alloy |
| Material of adjusting screw | Brass |
| Nut material | Wrought aluminum alloy |
| Swivel joint material | Die-cast zinc |