

Illuminating seal MEB-LD-12-24DC

Part number: 151717

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Switching position indication	LED
Type of mounting	On air solenoid valve with M2.5 central screw
Product weight	0.6 g
Electrical connection	Form C as per DIN EN 175301-803 Rectangular design MSEB
DC operating voltage range	12 V ... 24 V
Protective earth connection	Available
Nominal power luminous seal	0.05 W
Degree of protection	IP65
Ambient temperature	-25 °C ... 85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	TPE-U(PU)
Color	Transparent