

Profile strip SLMS-16- -

Part number: 152744

FESTO



 [General operating condition](#)

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Design	T-slot for proximity sensor
Max. profile length	2800 mm
Mounting position	Any
for piston Ø	Ø16
Structural design	Sensor rail
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C ... 60 °C
Type of mounting	With through-hole and screw
Profile material	Wrought aluminum alloy Anodized
Note on materials	RoHS-compliant
Material of screws	High-alloy steel