

# Manifold sub-base with 90° connections NAVW-3/8-2-ISO

Part number: 152790

FESTO



 General operating condition

## Data sheet

Feature	Value
Mounting position	Any
Conforms to standard	ISO 5599-1
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:2]
Information on operating and pilot media	Ester oil < 0.1mg/m <sup>3</sup> , according to ISO 8573-1:2010 [-:-:2]
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 80 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	550 g
Sub-base mounting type	With through-hole
Type of mounting	With through-hole
Pilot air port 12/14	G1/8
Auxiliary pilot air port 12	G1/8
Auxiliary pilot air port 14	G1/8
Pilot air port 12	G1/8
Pilot air port 14	G1/8
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Pneumatic connection 4	G3/8
Material of sub-base	Die-cast aluminum