

Manifold sub-base with 90° connections NAVW-1/4-NPT-1

Part number: 152792

FESTO



 General operating condition

Data sheet

Feature	Value
Width	110 mm
Mounting position	Any
Operating pressure	0 MPa ... 1.6 MPa
Operating pressure	0 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Ester oil < 0.1mg/m ³ , according to ISO 8573-1:2010 [-:-:2]
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C ... 80 °C
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Sub-base mounting type	With through-hole
Type of mounting	With through-hole
Pilot air port 12/14	1/8 NPT
Auxiliary pilot air port 12	1/8 NPT
Auxiliary pilot air port 14	1/8 NPT
Pilot air port 12	1/8 NPT
Pilot air port 14	1/8 NPT
Pneumatic connection 1	1/4 NPT
Pneumatic connection 2	1/4 NPT
Pneumatic connection 4	1/4 NPT
Material of sub-base	Die-cast aluminum