

Pressure gauge MA-15-10-QS-8

Part number: 153385

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Display range	0 bar ... 10 bar
Symbol	00991463
Pressure gauge nominal size	15
Structural design	Bourdon tube pressure gauge without measuring mechanism
Type of mounting	In-line installation
Operating medium	Inert gases Neutral liquids
Information on operating and pilot media	No acetylene No oxygen
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating pressure	0 psi ... 145 psi
Intermittent load factor	0.66
Measurement accuracy class	5
Degree of protection	IP53
Temperature of medium	-20 °C ... 60 °C
Ambient temperature	-20 °C ... 60 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Connection position	Centered on rear side
Pneumatic connection	QS-8
Materials in contact with the media	Brass
Material of screwed plug	Brass
Housing material	Steel
Inspection window material	PC
Housing colour	Black
Product weight	10 g
Scale	Single scale bar (außen)