

# Non return valve H-QS-8

Part number: 153464

FESTO



 [General operating condition](#)

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function                                    | Non-return function  |
| Pneumatic connection 1                            | QS-8   |
| Pneumatic connection 2                            | QS-8   |
| Type of mounting                                  | Line installation  |
| Normal nominal flow rate (normalized to DIN 1343) | 681 l/min  |
| Operating pressure                                | -1 bar ... 10 bar  |
| Ambient temperature                               | 0 °C ... 60 °C   |
| Housing material                                  | Aluminum, anodized   |
| Housing colour                                    | Black  |
| Operating medium                                  | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Symbol  | 00991455   |
| Min. differential pressure, opening               | 0.1 bar  |
| Min. differential pressure, closing               | 0.2 bar  |
| Information on operating and pilot media          | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity                            | VDMA24364-B1/B2-L  |
| Product weight                                    | 21 g   |
| Note on materials                                 | RoHS-compliant   |