

Push-in T-fitting QSYL-1/2-1/2-U

Part number: 153793

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal width	10.8 mm
Type of seal on screwed plug	Coating
Mounting position	Any
Design	L-shape, dual, parallel
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	75 g
No. of outlets	2
No. of supply lines	1
Type of mounting	External hexagon 7/8
Pneumatic connection 1	external thread 1/2 NPT
Pneumatic connection 2	for pneumatic tubing outside diameter 1/2"
Ambient temperature Fahrenheit	14 °F ... 140 °F
Releasing ring color	Gray
Note on materials	RoHS compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	high-alloy stainless steel