

# Push-in cap QSC-1/2-U

Part number: 153833

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Standard
Nominal width	7.8 mm
Tubing insertion depth	23.2 mm
Mounting position	Any
Design	Blanking plug
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	12 g
Pneumatic connection 1	For pneumatic tubing outside diameter 1/2"
Ambient temperature Fahrenheit	14 °F ... 140 °F
Releasing ring color	Gray
Note on materials	RoHS-compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel