

# Sensor bracket DASI-Q11-40-A-SR

Part number: 1548054

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Size	40
Design	for T-slot
for piston $\varnothing$	$\varnothing 40$
Structural design	Sensor rail
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Product weight	62 g
Type of mounting	Clamped in T slot With through-hole and screw With slot nuts
Note on materials	RoHS-compliant
Material of screws	Steel Galvanized