

Sensor bracket DASI-Q11-35-A-SR

Part number: 1550870

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|--|
| Size | 35 |
| Design | For T-slot |
| for piston \varnothing | $\varnothing 35$ |
| Structural design | Sensor rail |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 62 g |
| Type of mounting | Clamped in T slot With through-hole and screw With slot nuts |
| Note on materials | RoHS compliant |
| Material of screws | Steel Galvanized |