

Barb tubing fitting N-1/8-P-6-MS

Part number: 15630

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Nominal width | 4.5 mm |
| Type of seal on screwed plug | Sealing ring |
| Mounting position | Any |
| Design | Straight design |
| Pack size | 10 |
| Operating pressure for entire temperature range | -0.95 bar ... 16 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 5 Nm |
| Product weight | 10.17 g |
| Pneumatic connection 1 | External thread G1/8 |
| Pneumatic connection 2 | For tubing I.D. 6 mm |
| Note on materials | RoHS-compliant |
| Housing material | Brass |