

Clevis flange SUA-50

Part number: 157324

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|----------------------------------|
| Size | 50 |
| Mounting position | Any |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -40 °C ... 90 °C |
| Product weight | 288 g |
| Note on materials | RoHS-compliant |
| Mounting material | Wrought aluminum alloy |
| Bolt material | Steel, galvanized |
| Sleeve material | Spring steel |
| Material of bearing | Polymer |
| Material of screws | Steel, galvanized |
| Fuse material | Spring steel |
| Shaft material | Steel With protective coating |