

Rotary actuator DRRD-32-180-FH-Y9A

Part number: 1578518

FESTO



 General operating condition

Data sheet

Feature	Value
Size	32
Cushioning angle	82 deg
Setting range of swivel angle for each end position	+10 /-190 deg
Swivel angle	180 deg
Cushioning	Internal hydraulic cushioning normal
Mounting position	Any
Structural design	Gear rack/pinion
Position sensing	For proximity sensor
Symbol	00991265
Operating pressure	0.2 MPa ... 1 MPa
Operating pressure	2 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-10 °C ... 60 °C
Theoretical torque at 6 bar	10.1 Nm
Permissible mass moment of inertia	2.6 kgm ²
Product weight	2976 g
Type of mounting	With through-hole With internal thread
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Drive shaft material	Tempered steel
Cover material	Wrought aluminum alloy Anodized
Seals material	NBR TPE-U (PU)
Housing material	Smooth anodized