

Parallel kit EAMM-U-86-D40-60G-102

Part number: 1586445

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	86
Mounting position	Any
Gear ratio	1:1
Max. rotational speed	5000 rpm
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	175 kgmm ²
No-load driving torque	0.25 Nm
Transferable torque	9.5 Nm
Product weight	2480 g
Interface code, actuator	D40B
Interface code, motor in	60G
Note on materials	RoHS compliant