

Vacuum filter VAF-PK-4

Part number: 15889

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	3 mm
Mounting position	Any
Grade of filtration	50 µm
Symbol	00991483
Operating pressure	-0.95 bar ... 0 bar
Information on operating pressure	Only for use in open vacuum systems
Flow rate at negative pressure = -0.75 bar	70 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	0 °C ... 40 °C
Product weight	6 g
Type of mounting	In-line installation
Pneumatic connection	PK-4 with union nut
Material of union nut	POM
Note on materials	RoHS compliant
Compressed air filter material	Fabric PA
Housing material	PA
Ejector pulse suitability	≤8 bar