

# Parallel kit EAMM-U-110-S95-80G-207

Part number: 1589544

FESTO



 [General operating condition](#)

## Data sheet

| Feature                  | Value                 |
|--------------------------|-----------------------|
| Size                     | 110                   |
| Mounting position        | Any                   |
| Gear ratio               | 1:1                   |
| Max. rotational speed    | 5000 rpm              |
| LABS (PWIS) conformity   | VDMA24364 Zone III    |
| Storage temperature      | -25 °C ... 60 °C      |
| Relative air humidity    | 0 - 95%               |
| Degree of protection     | IP40                  |
| Ambient temperature      | -10 °C ... 60 °C      |
| Mass moment of inertia   | 799 kgmm <sup>2</sup> |
| No-load driving torque   | 0.3 Nm                |
| Transferable torque      | 25 Nm                 |
| Product weight           | 6940 g                |
| Interface code, actuator | S95                   |
| Interface code, motor in | 80G                   |
| Note on materials        | RoHS compliant        |