

Air reservoir CRVZS-0.1

Part number: 160233

FESTO



 General operating condition

Data sheet

Feature	Value
Volume	0.1 l
Mounting position	Any
Conforms to standard	AD 2000
Symbol	00991528
Operating pressure	-0.095 MPa ... 1.6 MPa
Operating pressure	-0.95 bar ... 16 bar
Operating pressure	-13.78 psi ... 232 psi
Certification	TÜV
Operating medium	Compressed air as per ISO 8573-1:2010 [-:-:-] Nitrogen
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 100 °C
Ambient temperature	-10 °C ... 100 °C
Max. tightening torque for connecting thread	15 Nm
Product weight	226 g
Type of mounting	Fixing clips
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Air reservoir material	high-alloy stainless steel
Fixing clips material	high-alloy stainless steel