


Push-in L-connector QSL-V0-8

Part number: 160541

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|---|
| Size | Standard |
| Nominal width | 7.2 mm |
| Material fire test | UL94 V-0 (housing) UL94 V-0 (releasing ring) |
| Design | L-shape |
| Pack size | 10 |
| Structural design | Push-pull principle |
| Operating pressure for entire temperature range | -0.095 MPa ... 1 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 145 psi |
| Information on operating pressure | Water: max. 0.6 MPa at max. 50 °C |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free) |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C ... 60 °C |
| Product weight | 13 g |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 8 mm |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 8 mm |
| Releasing ring color | Black |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | PBT |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel Brass |