


# Push-in L-connector QSL-V0-8

Part number: 160541

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	Standard
Nominal width	7.2 mm
Material fire test	UL94 V-0 (housing) UL94 V-0 (releasing ring)
Design	L-shape
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1 MPa
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating pressure for entire temperature range	-13.775 psi ... 145 psi
Information on operating pressure	Water: max. 0.6 MPa at max. 50 °C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C ... 60 °C
Product weight	13 g
Pneumatic connection 1	for pneumatic tubing outside diameter 8 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Releasing ring color	Black
Note on materials	RoHS compliant
Housing material	PBT
Releasing ring material	PBT
Material of tubing seal	NBR
Material of tube retaining claw	high-alloy stainless steel Brass