

Pneumatic muffler UC-1/8

Part number: 161419

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Pack size	1
Symbol	00991473
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	1700 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	59 dB(A)
Ambient temperature	-10 °C ... 70 °C
Product weight	2.6 g
Pneumatic connection	G1/8
Cushioning insert material	PE
Material of screwed plug	PE PP
Note on materials	RoHS-compliant