

Angled plug socket MPPE-3-B

Part number: 161839

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Contact durability	500
Type of mounting	With union nut
Mounting position	Any
Product weight	65 g
Electrical connection	8-pin Socket, angled Solderable
DC operating voltage range	≤60 V
Current rating	5 A
Cable fitting	Pg9
Approved cable diameter	6 mm ... 8 mm
Connection cross section	0.75 mm ²
Degree of protection	IP67
Ambient temperature	-30 °C ... 95 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Housing material	PA
Housing colour	Black
Material of union nut	PA
Material of pin contacts	Copper Tin-plated